



## Q caloric 5.5

Electronic device for recording the share of heat output by radiators.

In terms of measuring technology, the Q caloric 5.5 is 100% compatible with the Q caloric 5. All assembly-related properties also match the Q caloric 5.

The Q caloric 5.5 has improved and extended wireless properties. Available as a compact and remote sensor variant.

## Application

---

The Q caloric 5.5 is the successor model to the tried-and-trusted Q caloric 5. In addition to improved energy management, the Q caloric 5.5 can be operated in different wireless modes. In terms of measuring technology, the Q caloric 5.5 is 100% compatible to the Q caloric 5. Installation instructions can be taken over from the Q caloric 5 without changes being necessary. Communication with the current software versions of the Q suite 5 caloric (V2.1 or higher) and ACT46 (V1.6 or higher) is possible without restrictions.

In S-mode (Q walk-by & Q AMR), the Q caloric 5.5 is 100% compatible to the Q caloric 5. In C-mode (Q walk-by & Q AMR) the wireless capacities and ranges have been significantly improved compared to the Q caloric 5 in S-mode.

The electronic heat cost allocator Q caloric 5.5 has been designed for decentralised use. Values are measured by one or two temperature sensors. In 1-sensor operation only the radiator temperature is measured and a constant value is prescribed for the ambient temperature. In 2-sensor operation the actual difference in temperature between the ambient temperature and the radiator temperature is determined.

These measured values are used as a basic for calculation of the consumption calculation. The main area of application is in central heating systems where the heating energy is used individually by different consumers. The electronic heat cost allocator can be operated as a 1-sensor measuring system or 2-sensor measuring system with product and unit scale.

Such systems are used in e.g.:

- › Apartment buildings
- › Offices and administration buildings

Typical users are:

- › Meter reading service companies
- › Housing industry and housing associations
- › Building service companies and property management

The heat cost allocator can be used for the following types of radiator:

- › Ribbed radiators
- › Tubular radiators
- › Panel-type radiators with horizontal and vertical water flow
- › Radiators with internal tube register
- › Convector

## Q AMR

---

The electronic heat cost allocators Q caloric 5.5 type P2 and P3 are equipped with the Q AMR radio transmitter of the WHE4x device family.

The rcu4 radio system is not supported by the Q caloric 5.5.



---

In Q AMR (C-mode) the electronic heat cost allocator Q caloric 5.5 transmits OMS telegrams (OMS = Open Metering System) parallel to the walk-by telegrams. The OMS telegrams meet the "Open Metering System Specification" and can thus be received by all OMS-compatible devices.

## Data interface

The electronic heat cost allocators Q calorific 5.5 type P2 and P3 can be equipped with the IrDA close-range interface of the device family WHE3x/WHE4x.

The 1107 data interface is not supported by the Q calorific 5.5.

## Programming accessories

The programming accessories are used for communication with the metering devices.

### Programming adapter:

The programming adapter can be used as an individual programming tool and as a combi-adapter with the IrDA programming and readout head.

### IrDA programming and readout head<sup>(\*)</sup>:

The IrDA programming and readout head is used as a communication tool between a PC/netbook and the meter. The meter can be programmed and read out using the Q suite 5 calorific (V2.1 or higher).

(\*) Only necessary for meters without an integrated IrDA close-range interface.

## Programming possibilities

The following information can be programmed before the measuring device is put into operation:

### Standard parameters

- › Sensor type  
1-sensor or 2-sensor measuring system
- › K-value / KC / KQ  
Evaluation factors for calculating radiator heat output  
(depending on the meter algorithm and sensor type)
- › Next due date  
Day the annual value is stored  
(can also be programmed without IrDA interface using the programming adapter)
- › Device name / device code  
Device access data as protection from unauthorised device access

## Type overview


System	Article number
Q calorific 5.5 (P2) - profile compatibility HKVE 20x	HCA5 xx0x xxxx xxxx x
Q calorific 5.5 (P3) - profile compatibility WHEx	HCA5 xx3x xxxx xxxx x
S-mode (Q AMR, Q walk-by)	HCA5 xxxN xxxx xxxx x
C-mode (Q AMR, Q walk-by)	HCA5 xxxT xxxx xxxx x

For product variants see current price list

## Displays

Device states, consumption values and measuring system information are displayed on the LCD in a display loop.


Display loops in normal operation:



## Displays

The meters are delivered from the factory in sleep mode. Measuring operation is inactive.

Device display loops in sleep mode



## Displays

### Special displays P2/P3

#### Error messages

"Err 1" appears permanently. All other error messages are displayed in quick succession alternating with consumption values.



#### End of battery run time

Is displayed after the end of service life, alternating with the consumption values, depending on programming.



#### Manipulation or housing opening

Is displayed in the event of manipulation either as plain text alternating with the consumption values or by the indicator "c" shown discreetly on all displays, depending on programming.


Example: Display "current value" with "c".



#### Data interface

(IrDA close-range interface)

This display signalises an active IrDA close-range interface.




#### Radio system activated

S-mode: Q walk-by & Q AMR

C-mode: Q walk-by & Q AMR

The transmission of installation telegrams is indicated in this display.

Display sequence: InSt8, InSt7, ... InSt1



#### Commissioning

This display appears following clipping to the installation plate.

Then the display changes to the normal mode display loop.



**Remote sensor code**  
 The metering device has detected a remote sensor and adjusts its measuring behaviour accordingly.



## Radio (wireless) features S-mode

- › Radio system – parallel transmission of Q walk-by and Q AMR data telegrams
- › Transmission delay (offset)  
Time delay for sending telegrams after the due date or at the beginning of the month in days (standard = 0 days)
- › Transmission-free day  
A maximum of 2 days from Friday, Saturday and Sunday can be defined as transmission-free days  
At least 1 day must be set (standard = Sunday).
- › No change with the remote sensor system

Transmission behaviour	
<b>Q walk-by<sup>(*)</sup></b>	<b>Q AMR</b>
every 128 seconds	every 4 hours
10 hours per day (8 am - 6 pm)	24 hours per day
monthly: 4 readout dates after the first day of each month	7 days per week
annual: 48 hours after due date	365 days per year
current consumption values 13 Statistic values	data telegrams or statistics and consumption values

(\*) Compatible with Q caloric 5 / transmission delay or transmission-free days for Q walk-by only available in S-mode.

## Radio (wireless) features C-mode

- › Radio system – parallel transmission of Q walk-by and Q AMR data telegrams
- › Increased radio capacity in C-mode (10 dBm)
- › No change with the remote sensor system

Transmission behaviour	
<b>Q walk-by<sup>(1)</sup></b>	<b>Q AMR</b>
every 112 seconds	every 7.5 minutes
10 hours per day (8 am - 6 pm)	24 hours per day
365 days per year	365 days per year
current consumption values 13 Statistic values	current consumption values

(1) You need the mobile data collector Q log 5.5 and the readout software ACT46.PC V1.6 or higher for this.

The readout software can be downloaded from <http://qdc.qundis.com>.

## Mode change

It is possible to change between S-mode and C-mode in both directions.

For this, you need the Q suite 5 caloric (V2.1 or higher), a programming adapter<sup>(\*)</sup> or an IrDA programming and readout head.

(\*) Programming adapter and IrDA programming and readout head necessary for meters without an integrated IrDA close-range interface.

## Technical data

### Standards

	QUNDIS GmbH hereby declares that the Q calorific 5.5 complies with directive 2014/53/EU. The complete text of the EU Declaration of Conformity is available at the following internet address: <a href="http://www.qundis.com">www.qundis.com</a>
Product standard	DIN EN 834
RoHS-compliant	EN 50581
Type approval per HKVO [German heating costs legislation]	A1.01.2011 - Q calorific 5.5 - P2 C3.01.2011 - Q calorific 5.5 - P3

### Environment

Protection rating	IP43 per EN 60529
Protection class	III per EN 61140
Transport	-25 °C to +70 °C, < 95 % r.h. (without condensation) according to EN 60721-3-2
Storage	-5 °C to +45 °C, < 95 % r.h. (without condensation) according to EN 60721-3-1
Use	+5 °C to +55 °C, < 95 % r.h. (without condensation) according to EN 60721-3-3

### Radio

Radio mode	S-mode (Q AMR, Q walk-by) C-mode (Q AMR, Q walk-by)
Radio frequency	S-mode (868.30 +/- 0.30) MHz C-mode (868.95 +/- 0.25) MHz
Transmission power	S-mode (max. 14 dBm / typ. 7 dBm) C-mode (max. 14 dBm / typ. 10 dBm)
Data transmission per	EN 13757-4

### Electromagnetic compatibility

Interference resistance	EN 301489-1, EN 301489-3
Emitted interference	EN 301489-1, EN 301489-3
Security of IT equipment	EN 62368-1

### Supply

Battery type	Lithium metal
Operating voltage	DC 3 V
Battery service life	10 years operation + 1 year reserve + 6 months storage

### Display

Display	Liquid crystal display (LCD)
Scope of display	5 digits (00000 - 99999)

### Measuring system

Scaling	Product or unit scale
Radiator output range	Algorithm 2: 21 - 9999 Watts Algorithm 3/4: 21 - 5500 Watts
Temperature sensor	NTC (pre-aged)
1 sensor	With dynamic heating operating detection
2 sensors	1 sensor for radiator temperature and 1 sensor for room air temperature
Sensor temperature range	0 °C - 105 °C
tm-max	105 °C
tm-min <sup>(*)</sup>	35 °C (2-sensor system), 55 °C (1-sensor system)
Algorithm 2	1-sensor measuring system 255 values (basis: K-level 26) 2-sensor measuring system 999 values (basis: K-level 60)
Algorithm 3/4	1-sensor measurement system for repair and extension installations 2-sensor measurement system for repair and extension installations

<sup>(\*)</sup> mean design temperature

## Technical features

### Material

Dimensions (W x H x D)	40 x 102 x 30 mm
Remote sensor cable length	1.5 m / 2.5 m / 5.0 m
Device weight	55 g
Housing material	Polycarbonate (PC) + ABS plastic
Housing colours	White (satin)



### Installation

Device versions	Compact device Remote sensor device (compact device with optional remote sensor inserted)
New installation and conversion	Q caloric 5.5 with installation material provided
Standard replacement, extension installation and repair replacement	Q caloric 5.5 with installation material following the product families HKVE 20x and WHE3x/WHE4x




For the purposes of disposal, the device is considered a used electronics device in the sense of European directive 2012/19/EU and shall not be disposed of with household waste.  
 - Dispose of the device through the appropriate channels.  
 - Comply with local and currently valid legislation.  
 - Dispose of used batteries at a dedicated collection point.


## Dimensioning drawing of the device




Type P3



Type P2



## Dimensioning drawing of the snap-on panel



## Restrictions

Electronic heat cost allocators cannot be used with steam heaters, fresh-air radiators, underfloor heating, ceiling heating elements or flap-controlled radiators.

In the case of combined valve and flap-controlled radiators, metering devices may only be installed if the flap control unit has been removed or disabled in the "open" position.

Convector that can change their output through an electric fan and towel heaters with an electric heating cartridge must not be fitted with electronic heat cost allocators unless the respective electric system has been removed or disabled.

### 1-sensor and 2-sensor metering system

A joint use of different metering device types is only allowed within a property as long as they all use a standard metering system and have a standard measuring algorithm.

### Compatibility

The 202R can NOT be replaced by the Q caloric 5.5 Q AMR since the radio transmitter fitted in the heat cost allocator is not compatible with the rcu4 system.

Equally, the WHE2 can NOT be replaced by the Q caloric 5.5, since both the measuring algorithm and the radio transmitter fitted in the heat cost allocator (with WHE26) are not compatible.

---

**✉ QUNDIS GmbH**

Sonnentor 2

D-99098 Erfurt

**📞 +49 (0) 361 26 280-0**

**📠 +49 (0) 361 26 280-175**

**✉ info@qundis.com**

**www.qundis.com**

Member of  
**noventic group**